









Wippenet 4-voudig (1+3)



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend (gelakt)	2184 01	1	38,71	06	4010337012184
 zuiver wit glanzend (gelakt)	2184 03	1	38,71	06	4010337012191
 zuiver wit mat (gelakt)	2184 27	1	38,71	06	4010337013396
 antraciet (gelakt)	2184 28	1	42,10	06	4010337012207
 kleur aluminium (gelakt)	2184 26	1	45,95	06	4010337012214
 zwart mat (gelakt)	2184 005	1	45,95	06	4010337038412
 grijs mat (gelakt)	2184 015	1	45,95	06	4010337083474
 edelstaal	2134 601	1	28,55	06	4010337020226

Aanwijzingen

- Beschrijfbare wippenets en wippenets zonder tekstkader zijn van metaal, dit kan bij draadloze toepassingen het bereik beperken.