










Wippenet 6-voudig (3+3)



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend (gelakt)	2186 01	1	57,68	06	4010337012221
 zuiver wit glanzend (gelakt)	2186 03	1	57,68	06	4010337012238
 zuiver wit mat (gelakt)	2186 27	1	57,68	06	4010337013402
 antraciet (gelakt)	2186 28	1	62,68	06	4010337012245
 kleur aluminium (gelakt)	2186 26	1	68,39	06	4010337012252
 zwart mat (gelakt)	2186 005	1	68,39	06	4010337038474
 grijs mat (gelakt)	2186 015	1	68,39	06	4010337083825
 edelstaal	2136 601	1	40,00	06	4010337020332

Aanwijzingen

- Beschrijfbare wippenets en wippenets zonder tekstkader zijn van metaal, dit kan bij draadloze toepassingen het bereik beperken.