











Luidspreker inbouwradio



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|----|--------------------|----|---------------|
|  crème wit glanzend | 2282 01 | 1 | 27,64 | 03 | 4010337076230 |
|  zuiver wit glanzend | 2282 03 | 1 | 27,64 | 03 | 4010337076247 |
|  zuiver wit mat | 2282 27 | 1 | 27,64 | 03 | 4010337076254 |
|  antraciet | 2282 28 | 1 | 29,76 | 03 | 4010337076261 |
|  kleur aluminium | 2282 26 | 1 | 32,42 | 03 | 4010337076162 |
|  in zwartglaslook | 2282 05 | 1 | 37,20 | 03 | 4010337889182 |
|  zwart mat | 2282 005 | 1 | 32,42 | 03 | 4010337037286 |
|  grijs mat | 2282 015 | 1 | 32,42 | 03 | 4010337083931 |
|  edelstaal | 2282 600 | 1 | 37,20 | 03 | 4010337032861 |

Kenmerken

- Luidspreker voor aansluiting op de Gira inbouwradio.

Technische gegevens

| | |
|---|--------------------|
| Inbouwdiepte: | 32 mm |
| Aansluitingdoorsnede - Luidspreker-/AUX-aansluiting: | 1.5mm ² |
| Impedantie: | 8 Ω |
| Omgevingstemperatuur: | -5 °C tot +50 °C |
