








Tastchakelaar 10 AX 250 V~met rechtstaande wip 2-voudig Serieschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	2860 201	1/5	28,37	01	4010337065876
 zuiver wit mat	2860 27	1/5	28,37	01	4010337029373
 antraciet	2860 28	1/5	28,88	11	4010337029397
 kleur aluminium	2860 26	1/5	32,08	11	4010337029380
 zwart mat	2860 005	1/5	32,08	11	4010337038023
 grijs mat	2860 015	1/5	32,08	11	4010337087199
 edelstaal	2860 600	1/5	39,15	11	4010337021223

Technische gegevens

Inbouwdiepte	
- 2860 ...	28 mm
- 2861 ...	32 mm
Aansluitingdoorsnede	
- voor stijve en flexibele geleiders tot:	2.5mm ²
Nominaal vermogen	
- LEDi/ CFLi:	100 W

Afbeeldingen zijn gelijkend en kunnen van het origineel afwijken.
Prijzen geldig voor België met prijzen per 01/24.

Aanwijzingen

- Volgens beschikbaarheid.
