






Tastschakelaar 10 AX 250 V~met rechtstaande wip 2-voudig
Wisselschakelaar 2-voudig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	2861 201	1/5	40,02	01	4010337065883
 zuiver wit mat	2861 27	1/5	40,02	01	4010337053286
 antraciet	2861 28	1/5	40,54	11	4010337053293
 kleur aluminium	2861 26	1/5	43,74	11	4010337053279
 edelstaal	2861 600	1/5	50,74	11	4010337021209

Technische gegevens

Inbouwdiepte	
- 2860 ...:	28 mm
- 2861 ...:	32 mm
Aansluitingdoorsnede	
- voor stijve en flexibele geleiders tot:	2.5mm ²
Nominaal vermogen	
- LEDi/ CFLi:	100 W

Aanwijzingen

- Volgens beschikbaarheid.