











Wippenet 2-voudig voor tastsensor 4.95



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 aluminium zuiver wit glanzend (gelakt)	5022 903	1	102,88	06	4010337098577
 aluminium zuiver wit mat (gelakt)	5022 927	1	102,88	06	4010337098607
 aluminium antraciet (gelakt)	5022 928	1	102,88	06	4010337098515
 aluminium (geanodiseerd)	5022 17	1	78,67	06	4010337072331
 aluminium zwart mat (gelakt)	5022 905	1	102,88	06	4010337098546
 aluminium grijs mat (gelakt)	5022 915	1	102,88	06	4010337098485
 aluminium zwart (geanodiseerd)	5022 126	1	78,67	06	4010337072188
 brons	5022 38	1	181,56	06	4010337098638
 glas wit	5022 12	1	78,67	06	4010337072041



glas zwart

5022 05

1

78,67

06

4010337071990



edelstaal

5022 219

1

145,24

06

4010337072072