









Wip 2-voudig audiobesturing System 55



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|-----|--------------------|----|---------------|
|  crème wit glanzend | 5384 01 | 1/5 | 12,34 | 02 | 4010337122739 |
|  zuiver wit glanzend | 5384 03 | 1/5 | 12,34 | 02 | 4010337122746 |
|  zuiver wit mat | 5384 27 | 1/5 | 12,34 | 02 | 4010337122753 |
|  antraciet | 5384 28 | 1/5 | 14,96 | 02 | 4010337122760 |
|  kleur aluminium | 5384 26 | 1/5 | 16,79 | 02 | 4010337122777 |
|  zwart mat | 5384 005 | 1/5 | 16,79 | 02 | 4010337122784 |
|  grijs mat | 5384 015 | 1/5 | 16,79 | 02 | 4010337122791 |
|  edelstaal | 5384 600 | 1/5 | 19,99 | 02 | 4010337122807 |

Kenmerken

- Wippen als vervanging voor de originele wip met symbolen.
 - Universeel te gebruiken voor de linker en rechter wip.
-

Aanwijzingen

- Bij gebruik van een opzetstuk van metaal en/of een afdekraam van metaal kan het bereik nadelig worden beïnvloed.
-