










Draagring Modular Jack 2-voudig Draagring MJ-01 tot MJ-10



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 Draagring MJ-01	5601 00	10	7,27	01	4010337460015
 Draagring MJ-02	5602 00	10	7,27	01	4010337460022
 Draagring MJ-03	5603 00	10	7,27	01	4010337460039
 Draagring MJ-04	5604 00	10	7,27	01	4010337460046
 Draagring MJ-05	5605 00	10	7,27	01	4010337460053
 Draagring MJ-06	5606 00	10	7,27	01	4010337460060
 Draagring MJ-07	5607 00	10	7,27	01	4010337460077
 Draagring MJ-08	5608 00	10	7,27	01	4010337460084
 Draagring MJ-09	5609 00	10	7,27	01	4010337460091



Draagring MJ-10

5610 00

10

7,27

01

4010337460107

Aanwijzingen

- Uitsluitend voor schroefbevestiging.
- Geschikt voor wandgootinstallatie.

Afmetingen in mm

MJ-01, MJ02, MJ-07:	B 14,8	H 19,5
MJ-03:	B 14,8	H 20,0
MJ-04, MJ-09:	B 14,8	H 19,3
MJ-05:	B 16,7	H 17,3
MJ-06:	B 15,9	H 18,3
MJ-08:	B 14,8	H 19,0
MJ-10:	B 16,1	H 18,5
