










## Draagring Modular Jack 2-voudig Draagring MJ-01 tot MJ-10



| Specificatie  | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|---|----------|----|--------------------|----|---------------|
|  Draagring MJ-01  | 5601 00  | 10 | 7,27               | 01 | 4010337460015 |
|  Draagring MJ-02 | 5602 00  | 10 | 7,27               | 01 | 4010337460022 |
|  Draagring MJ-03 | 5603 00  | 10 | 7,27               | 01 | 4010337460039 |
|  Draagring MJ-04 | 5604 00  | 10 | 7,27               | 01 | 4010337460046 |
|  Draagring MJ-05 | 5605 00  | 10 | 7,27               | 01 | 4010337460053 |
|  Draagring MJ-06 | 5606 00  | 10 | 7,27               | 01 | 4010337460060 |
|  Draagring MJ-07 | 5607 00  | 10 | 7,27               | 01 | 4010337460077 |
|  Draagring MJ-08 | 5608 00  | 10 | 7,27               | 01 | 4010337460084 |
|  Draagring MJ-09 | 5609 00  | 10 | 7,27               | 01 | 4010337460091 |



Draagring MJ-10

5610 00

10

7,27

01

4010337460107

---

## Aanwijzingen

- Uitsluitend voor schroefbevestiging.
- Geschikt voor wandgootinstallatie.

---

## Afmetingen in mm

|                     |        |        |
|---------------------|--------|--------|
| MJ-01, MJ02, MJ-07: | B 14,8 | H 19,5 |
| MJ-03:              | B 14,8 | H 20,0 |
| MJ-04, MJ-09:       | B 14,8 | H 19,3 |
| MJ-05:              | B 16,7 | H 17,3 |
| MJ-06:              | B 15,9 | H 18,3 |
| MJ-08:              | B 14,8 | H 19,0 |
| MJ-10:              | B 16,1 | H 18,5 |

---