










## Wip voor wippenet 2-voudig voor tastsensor 4.95



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 aluminium zuiver wit glanzend (gelakt)	8332 903	1	56,06	06	4010337098713
 aluminium zuiver wit mat (gelakt)	8332 927	1	56,06	06	4010337098737
 aluminium antraciet (gelakt)	8332 928	1	56,06	06	4010337098676
 aluminium (geanodiseerd)	8332 17	1	44,26	06	4010337096979
 aluminium zwart mat (gelakt)	8332 905	1	56,06	06	4010337098690
 aluminium grijs mat (gelakt)	8332 915	1	56,06	06	4010337098652
 aluminium zwart (geanodiseerd)	8332 126	1	44,26	06	4010337096993
 brons	8332 38	1	94,42	06	4010337098751
 glas wit	8332 12	1	44,26	06	4010337097792

	glas zwart	8332 05	1	44,26	06	4010337098027
	edelstaal	8332 219	1	76,72	06	4010337097334