











Wip voor wippenet 2-voudig voor tastsensor 4



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|--|----------|----|--------------------|----|---------------|
|  aluminium zuiver wit glanzend (gelakt) | 8332 903 | 1 | 55,07 | 06 | 4010337098713 |
|  aluminium zuiver wit mat (gelakt) | 8332 927 | 1 | 55,07 | 06 | 4010337098737 |
|  aluminium antraciet (gelakt) | 8332 928 | 1 | 55,07 | 06 | 4010337098676 |
|  aluminium (geanodiseerd) | 8332 17 | 1 | 43,48 | 06 | 4010337096979 |
|  aluminium zwart mat (gelakt) | 8332 905 | 1 | 55,07 | 06 | 4010337098690 |
|  aluminium grijs mat (gelakt) | 8332 915 | 1 | 55,07 | 06 | 4010337098652 |
|  aluminium zwart (geanodiseerd) | 8332 126 | 1 | 43,48 | 06 | 4010337096993 |
|  brons | 8332 38 | 1 | 92,75 | 06 | 4010337098751 |
|  glas wit | 8332 12 | 1 | 43,48 | 06 | 4010337097792 |

| | | | | | | |
|---|------------|----------|---|-------|----|---------------|
|  | glas zwart | 8332 05 | 1 | 43,48 | 06 | 4010337098027 |
|  | edelstaal | 8332 219 | 1 | 75,36 | 06 | 4010337097334 |