







Drukcontact 10 A 250 V~ met rechtstaande wip met controlevenster
Wisselcontact 1-polig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	0120 201	1/5	25,77	11	4010337065982
 zuiver wit mat	0120 27	1/5	25,77	01	4010337029465
 antraciet	0120 28	1/5	26,69	11	4010337029489
 kleur aluminium	0120 26	1/5	30,69	11	4010337029472
 zwart mat	0120 005	1/5	30,69	11	4010337037927
 edelstaal	0120 600	1/5	39,15	11	4010337021247

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm ²

Aanwijzingen

- Ook verlichtbaar aan te sluiten.

- Volgens beschikbaarheid.
