






**Tast-controleschakelaar 10 AX 250 V~ met afdekking en wip
Uitschakelaar 2-polig**

Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0122 40 492033	1/5	43,23	01	4010337122401
 grijs	0122 42 492751	1/5	43,48	11	4010337122425
 rood	0122 43 493114	1/5	43,48	11	4010337122432
 blauw	0122 46 494195	1/5	43,48	11	4010337122463
 zwart	0122 47 494740	1/5	43,48	11	4010337122470

Kenmerken

- Glimlampenelement 230 V~, 1,5 mA is bij levering inbegrepen.

Technische gegevens

Inbouwdiepte: 28 mm

Aanwijzingen

- Ook met verlichting aan te sluiten.