

Tast-controleschakelaar 10 AX 250 V~ met afdekking en wip Schakelaar 2-polig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0122 40	1/5	61,43	01	4010337122401
 grijs	0122 42	1/5	61,78	11	4010337122425
 rood	0122 43	1/5	61,78	11	4010337122432
 blauw	0122 46	1/5	61,78	11	4010337122463
 zwart	0122 47	1/5	61,78	11	4010337122470

Kenmerken

- Glimlampelement 230 V~, 1,5 mA is bij de levering inbegrepen.

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm²
Nominaal vermogen - LEDi/ CFLi:	100 W

Aanwijzingen

- Ook verlichtbaar aan te sluiten.
