

## Tast-controleschakelaar 10 AX 250 V~ met afdekking en wip Schakelaar 2-polig



| Specificatie                                                                                  | Art. nr. | VE  | EUR/stuk excl. BTW | PS | EAN           |
|-----------------------------------------------------------------------------------------------|----------|-----|--------------------|----|---------------|
|  zuiver wit | 0122 40  | 1/5 | 61,43              | 01 | 4010337122401 |
|  grijs     | 0122 42  | 1/5 | 61,78              | 11 | 4010337122425 |
|  rood      | 0122 43  | 1/5 | 61,78              | 11 | 4010337122432 |
|  blauw     | 0122 46  | 1/5 | 61,78              | 11 | 4010337122463 |
|  zwart     | 0122 47  | 1/5 | 61,78              | 11 | 4010337122470 |

### Kenmerken

- Glimlampelement 230 V~, 1,5 mA is bij de levering inbegrepen.

### Technische gegevens

|                                                                   |                    |
|-------------------------------------------------------------------|--------------------|
| Inbouwdiepte:                                                     | 28 mm              |
| Aansluitingdoorsnede<br>- voor stijve en flexibele geleiders tot: | 2.5mm <sup>2</sup> |
| Nominaal vermogen<br>- LEDi/ CFLi:                                | 100 W              |

## Aanwijzingen

- Ook verlichtbaar aan te sluiten.

---