



Tastchakelaar 10 AX 250 V~met rechtstaande wip Kruisschakelaar



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|--|----------|-----|--------------------|----|---------------|
|  zuiver wit glanzend | 0123 201 | 1/5 | 35,35 | 01 | 4010337052708 |
|  zuiver wit mat | 0123 27 | 1/5 | 35,35 | 01 | 4010337029342 |
|  antraciet | 0123 28 | 1/5 | 36,18 | 11 | 4010337029366 |
|  kleur aluminium | 0123 26 | 1 | 40,13 | 11 | 4010337029359 |
|  zwart mat | 0123 005 | 1 | 40,13 | 11 | 4010337037996 |
|  grijs mat | 0123 015 | 1 | 40,13 | 11 | 4010337077114 |
|  edelstaal | 0123 600 | 1 | 48,97 | 11 | 4010337021254 |

Technische gegevens

| | |
|---|--------------------|
| Inbouwdiepte: | 28 mm |
| Aansluitingdoorsnede - voor stijve en flexibele geleiders tot: | 2.5mm ² |
| Nominaal vermogen - LEDi/ CFLi: | 100 W |

Aanwijzingen

- Volgens beschikbaarheid.
