








Tastchakelaar 10 AX 250 V~met rechtstaande wip Kruisschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	0123 201	1/5	35,35	01	4010337052708
 zuiver wit mat	0123 27	1/5	35,35	01	4010337029342
 antraciet	0123 28	1/5	36,18	11	4010337029366
 kleur aluminium	0123 26	1	40,13	11	4010337029359
 zwart mat	0123 005	1	40,13	11	4010337037996
 grijs mat	0123 015	1	40,13	11	4010337077114
 edelstaal	0123 600	1	48,97	11	4010337021254

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm ²
Nominaal vermogen - LEDi/ CFLi:	100 W

Aanwijzingen

- Volgens beschikbaarheid.
