







**Tast-controleschakelaar 10 AX 250 V~met rechtstaande wip
Universele uit-wisselschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	0124 201	1/5	43,13	01	4010337052715
 zuiver wit mat	0124 27	1/5	43,13	01	4010337029403
 antraciet	0124 28	1/5	43,89	11	4010337029427
 kleur aluminium	0124 26	1	47,78	11	4010337029410
 zwart mat	0124 005	1	47,78	11	4010337037958
 edelstaal	0124 600	1	56,62	11	4010337021230

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm ²
Nominaal vermogen - LEDi/ CFLi:	100 W

Aanwijzingen

- Ook verlichtbaar aan te sluiten.
 - Volgens beschikbaarheid.
-

Levering

- Glimlampelement 230 V~, 1,5 mA is bij de levering inbegrepen.
-