







**Tast-controleschakelaar 10 AX 250 V~met rechtstaande wip
Universele uit-wisselschakelaar**



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|--|----------|-----|--------------------|----|---------------|
|  zuiver wit glanzend | 0124 201 | 1/5 | 43,13 | 01 | 4010337052715 |
|  zuiver wit mat | 0124 27 | 1/5 | 43,13 | 01 | 4010337029403 |
|  antraciet | 0124 28 | 1/5 | 43,89 | 11 | 4010337029427 |
|  kleur aluminium | 0124 26 | 1 | 47,78 | 11 | 4010337029410 |
|  zwart mat | 0124 005 | 1 | 47,78 | 11 | 4010337037958 |
|  edelstaal | 0124 600 | 1 | 56,62 | 11 | 4010337021230 |

Technische gegevens

| | |
|---|--------------------|
| Inbouwdiepte: | 28 mm |
| Aansluitingdoorsnede - voor stijve en flexibele geleiders tot: | 2.5mm ² |
| Nominaal vermogen - LEDi/ CFLi: | 100 W |

Aanwijzingen

- Ook verlichtbaar aan te sluiten.
 - Volgens beschikbaarheid.
-

Levering

- Glimlampelement 230 V~, 1,5 mA is bij de levering inbegrepen.
-