










**Tastschakelaar 10 AX 250 V~ met 2-voudige wip  
Serieschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0125 01 2832707	1/5	25,96	01	4010337125013
 zuiver wit glanzend	0125 03 2832715	1/5	25,96	01	4010337125037
 zuiver wit mat	0125 27 1724723	1/5	25,96	01	4010337125273
 antraciet	0125 28 1724731	1/5	26,48	11	4010337125280
 kleur aluminium	0125 26 2109015	1/5	29,35	11	4010337125266
 zwart mat	0125 005 6914329	1/5	29,35	11	4010337038016
 grijs mat	0125 015	1/5		11	4010337077138
 edelstaal	0125 600 1147197	1/5	35,85	11	4010337021780
 brons	0125 603 4834883	1/5	39,48	11	4010337106012



messing

0125 604  
4835450

1/5

39,48

11

4010337106029



chrom

0125 605  
8758989

1/5

39,48

11

4010337000839

## Technische gegevens

Inbouwdiepte

- 0125 ...:

28 mm

- 0128 ...:

32 mm

Aansluitingdoorsnede

- voor geleiders tot:

2,5 mm<sup>2</sup>