

**Tastschakelaar 10 AX 250 V~ met afdekking en wip 2-voudig
Serieschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0125 40	1/5	41,06	01	4010337125402
 grijs	0125 42	1/5	41,28	11	4010337125426
 rood	0125 43	1/5	41,28	11	4010337125433
 blauw	0125 46	1/5	41,28	11	4010337125464
 zwart	0125 47	1/5	41,28	11	4010337125471

Technische gegevens

Inbouwdiepte	
- 0125 ...:	28 mm
- 0128 ...:	32 mm
Aansluitingdoorsnede	
- voor stijve en flexibele geleiders tot:	2.5mm²
Nominaal vermogen	
- LEDi/ CFLi:	100 W