






**Tastschakelaar 10 AX 250 V~ met afdekking en wip  
Universele uit-wisselschakelaar**

Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0126 40 492009	1/5	21,78	01	4010337126409
 grijs	0126 42 492728	1/5	21,88	11	4010337126423
 rood	0126 43 493080	1/5	21,88	11	4010337126430
 blauw	0126 46 494161	1/5	21,88	11	4010337126461
 zwart	0126 47 494716	1/5	21,88	11	4010337126478

**Technische gegevens**

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm <sup>2</sup>
Nominaal vermogen - LEDi/ CFLi:	100 W

**Aanwijzingen**

- Wanneer deze schakelaar moet worden verlicht, dan een controleschakelaar gebruiken.