






Tastschakelaar 10 AX 250 V~ met afdekking en wip
Universele uit-wisselschakelaar

| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|-------------------|-----|--------------------|----|---------------|
|  zuiver wit | 0126 40 492009 | 1/5 | 20,86 | 01 | 4010337126409 |
|  grijs | 0126 42 492728 | 1/5 | 20,96 | 11 | 4010337126423 |
|  rood | 0126 43 493080 | 1/5 | 20,96 | 11 | 4010337126430 |
|  blauw | 0126 46 494161 | 1/5 | 20,96 | 11 | 4010337126461 |
|  zwart | 0126 47 494716 | 1/5 | 20,96 | 11 | 4010337126478 |

Technische gegevens

| | |
|---|---------------------|
| Inbouwdiepte: | 28 mm |
| Aansluitingdoorsnede - voor geleiders tot: | 2,5 mm ² |

Aanwijzingen

- Wanneer deze schakelaar moet worden verlicht, dan een controleschakelaar gebruiken.