











**Tastchakelaar 10 AX 250 V~ met wip
Kruisschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0127 01 2832681	1/5	26,08	01	4010337127017
 zuiver wit glanzend	0127 03 2832699	1/5	26,08	01	4010337127031
 zuiver wit mat	0127 27 1724707	1/5	26,08	01	4010337127277
 antraciet	0127 28 1724715	1/5	26,62	11	4010337127284
 kleur aluminium	0127 26 2109007	1/5	29,50	11	4010337127260
 zwart mat	0127 005 6914343	1/5	29,50	11	4010337037989
 edelstaal	0127 600 1147204	1/5	36,01	11	4010337021759
 brons	0127 603 4834909	1/5	39,09	11	4010337106067
 messing	0127 604 4835476	1/5	39,09	11	4010337106074



chrom

0127 605
8759003

1/5

39,09

11

4010337000853

Technische gegevens

Inbouwdiepte:

28 mm
