






## Tastschakelaar 10 AX 250 V~ met afdekking en wip Kruisschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0127 40 492025	1/5	31,65	01	4010337127406
 grijs	0127 42 492744	1/5	31,82	11	4010337127420
 rood	0127 43 7692239	1/5	31,82	11	4010337127437
 blauw	0127 46 7692247	1/5	31,82	11	4010337127468
 zwart	0127 47 494732	1/5	31,82	11	4010337127475

### Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm <sup>2</sup>
Nominaal vermogen - LEDi/ CFLi:	100 W

### Aanwijzingen

- Wanneer deze schakelaar moet worden verlicht, dan een controleschakelaar gebruiken.