






Tastschakelaar 10 AX 250 V~ met afdekking en wip Kruisschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0127 40	1/5	37,40	01	4010337127406
 grijs	0127 42	1/5	37,59	11	4010337127420
 rood	0127 43	1/5	37,59	11	4010337127437
 blauw	0127 46	1/5	37,59	11	4010337127468
 zwart	0127 47	1/5	37,59	11	4010337127475

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele leidingen tot:	2,5 mm ²
Nominaal vermogen - LEDi/ CFLi:	100 W

Aanwijzingen

- Wanneer deze schakelaar moet worden verlicht, dan een controleschakelaar gebruiken.