










**Tastschakelaar 10 AX 250 V~ met 2-voudige wip**  
**Wisselschakelaar 2-voudig**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0128 01 2832723	1/5	36,83	01	4010337128014
 zuiver wit glanzend	0128 03 2832731	1/5	36,83	01	4010337128038
 zuiver wit mat	0128 27 2298537	1/5	36,83	01	4010337128274
 antraciet	0128 28 2298545	1/5	37,43	11	4010337128281
 kleur aluminium	0128 26 2298552	1/5	40,30	11	4010337128267
 zwart mat	0128 005 6914350	1/5	40,30	11	4010337038030
 grijs mat	0128 015	1/5		11	4010337077176
 edelstaal	0128 600 1146819	1/5	46,81	11	4010337021797

**Technische gegevens**

Inbouwdiepte  
- 0125 ...: 28 mm

- 0128 ...:	32 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm <sup>2</sup>

---