








**Drukcontact 10 A 250 V~ met rechtstaande wip
Wisselcontact 1-polig**

Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	0130 201	1/5	23,96	01	4010337066064
 zuiver wit mat	0130 27	1/5	23,96	01	4010337029434
 antraciet	0130 28	1/5	24,87	11	4010337029458
 kleur aluminium	0130 26	1/5	28,84	11	4010337029441
 zwart mat	0130 005	1/5	28,84	11	4010337037910
 grijs mat	0130 015	1/5	28,84	11	4010337077183
 edelstaal	0130 600	1/5	37,42	11	4010337035947

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm ²

Aanwijzingen

- Volgens beschikbaarheid.
