






**Tast-controleschakelaar 10 AX 250 V~ met afdekking en wip  
Universele uit-wisselschakelaar**

Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0136 40 492041	1/5	40,39	01	4010337136408
 grijs	0136 42 492769	1/5	40,65	11	4010337136422
 rood	0136 43 493122	1/5	40,65	11	4010337136439
 blauw	0136 46 494203	1/5	40,65	11	4010337136460
 zwart	0136 47 494757	1/5	40,65	11	4010337136477

**Kenmerken**

- Glimlampenelement 230 V~, 1,5 mA is bij levering inbegrepen.

**Technische gegevens**

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele leidingen tot:	2,5 mm <sup>2</sup>
Nominaal vermogen - LEDi/ CFLi:	100 W

## Aanwijzingen

- Ook met verlichting aan te sluiten.

---