








## Afdekraam Gira E2 antraciet



| Specificatie  | Art. nr. | VE     | EUR/stuk excl. BTW | PS | EAN           |
|---|----------|--------|--------------------|----|---------------|
|  1-voudig                     | 0211 23  | 10/100 | 9,78               | 11 | 4010337211235 |
|  1,5-voudig                  | 1001 23  | 10     | 14,53              | 11 | 4010337881339 |
|  2-voudig                    | 0212 23  | 10/100 | 14,99              | 11 | 4010337212232 |
|  2-voudig zonder middenstijl | 1002 23  | 10     | 14,99              | 11 | 4010337002239 |
|  3-voudig                    | 0213 23  | 1/5    | 24,46              | 11 | 4010337213239 |
|  4-voudig                    | 0214 23  | 1/5    | 39,41              | 11 | 4010337214236 |
|  5-voudig                    | 0215 23  | 1/5    | 60,27              | 11 | 4010337215233 |

### Aanwijzingen

- Ook geschikt voor wandgootinstallatie.
- Afdekraam (1- tot 5-voudig) in combinatie met afdichtset ook geschikt voor installatie spatwaterdicht inbouw IP44.