








Afdekraam Gira E2 kleur aluminium



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|-----------------------------------------------------------------------------------------------------------------|----------|--------|--------------------|----|---------------|
|  1-voudig | 0211 25 | 10/100 | 14,69 | 11 | 4010337211259 |
|  1,5-voudig | 1001 25 | 10 | 22,00 | 11 | 4010337881346 |
|  2-voudig | 0212 25 | 10 | 22,54 | 11 | 4010337212256 |
|  2-voudig zonder middenstijl | 1002 25 | 10 | 22,54 | 11 | 4010337002253 |
|  3-voudig | 0213 25 | 1/5 | 36,68 | 11 | 4010337213253 |
|  4-voudig | 0214 25 | 1/5 | 59,58 | 11 | 4010337214250 |
|  5-voudig | 0215 25 | 1/5 | 90,59 | 11 | 4010337215257 |

Aanwijzingen

- Ook geschikt voor wandgootinstallatie.
- Afdekraam (1- tot 5-voudig) in combinatie met afdichtset ook geschikt voor installatie spatwaterdicht inbouw IP44.