












Wip



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0296 01 2832780	10	3,85	21	4010337296010
 zuiver wit glanzend	0296 03 2832798	10	3,85	21	4010337296034
 zuiver wit mat	0296 27 1724988	10/100	3,85	21	4010337296270
 antraciet	0296 28 1724996	10	4,32	11	4010337296287
 kleur aluminium	0296 26 2109031	10	7,15	11	4010337296263
 zwart mat	0296 005 6913825	10	7,15	11	4010337038061
 grijs mat	0296 015	10		11	4010337080220
 edelstaal	0296 600 1146609	10	13,67	11	4010337021667
 brons	0296 603 4835278	10	15,93	11	4010337097747

	messing	0296 604 4835872	10	15,93	11	4010337097754
	chroom	0296 605 8759283	10	15,93	11	4010337001416

Aanwijzingen

- Afdekraam (1- tot 5-voudig) uit de schakelaarprogramma's Standard 55 en Gira E2 in combinatie met de afdichtset ook geschikt voor de spatwaterdichte (IP44) installatie van wipchakelaars en wipdrukcontacten (geldt niet voor 2-voudige wip).