







Wandcontactdoos stereo-luidspreker



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0402 01	1/5	21,33	01	4010337402015
 zuiver wit glanzend	0402 03	1/5	21,33	01	4010337402039
 zuiver wit mat	0402 27	1/5	21,33	01	4010337402275
 antraciet	0402 28	1/5	24,39	11	4010337402282
 kleur aluminium	0402 26	1/5	27,38	11	4010337402268
 zwart mat	0402 005	1/5	27,38	11	4010337037880

Kenmerken

- Met schroefklemmen.

Technische gegevens

Inbouwdiepte: 31 mm
Aansluitingdoorsnede max.: 1,5 mm²

Aanwijzingen

- Voor leidingdoorsnede tot max. 10 mm².
 - Te gebruiken als basiselement voor high-end luidsprekerconnectors (WBT) en datakap.
-