










## Wandcontactdoos met randaarde 16 A 250 V~



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0466 01 2833275	10	6,35	21	4010337466017
 zuiver wit glanzend	0466 03 2833283	10	6,35	21	4010337466031
 zuiver wit mat	0466 27 2309847	10/100	6,35	21	4010337466277
 antraciet	0466 28 2309854	10/100	6,96	11	4010337466284
 kleur aluminium	0466 26 2309862	10/100	11,28	11	4010337466260
 zwart mat	0466 005 6912985	10	11,28	11	4010337037644
 Edelstaal	0466 600 1145951	1	18,64	11	4010337034094
 brons-zwart	0466 603 4835310	1/5	21,57	11	4010337097884
 brons-crème wit	0466 613 4835328	1/5	21,57	11	4010337097914

	messing-zwart	0466 604 4835914	1/5	21,57	11	4010337097891
	messing-crème wit	0466 614 4835922	1/5	21,57	11	4010337097907
	chrom-zwart	0466 605 8759318	1/5	21,57	11	4010337001485
	chrom-crème wit	0466 615 8759325	1/5	21,57	11	4010337001492

## Technische gegevens

Inbouwdiepte: 32 mm

## Aanwijzingen

- Met verhoogde contactdruk van de aardbeugel gekeurd volgens TNO.