






Dubbele wandcontactdoos met randaarde 16 A 250 V~ met verhoogde aanraakbeveiliging (Safety Plus) en vaste afdekplaat voor inbouwapparaatdoos 1-voudig Steekklemmen



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0783 01	1	26,69	01	4010337783015
 zuiver wit glanzend	0783 03	1	26,69	01	4010337783039
 zuiver wit mat	0783 27	1	26,69	01	4010337783275
 antraciet	0783 28	1	29,85	11	4010337783282
 kleur aluminium	0783 26	1	34,65	11	4010337783268
 zwart mat	0783 005	1	34,65	11	4010337037507
 grijs mat	0783 015	1	34,65	11	4010337081876

Technische gegevens

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders van:	1,5 mm ² tot 2,5 mm ²
Omgevingstemperatuur - verhoogde aanraakbeveiliging:	0 °C tot +45 °C

Aanwijzingen

- Passend in alle gangbare apparaatdozen.
 - Verhoogde aanraakbeveiliging (Safety Plus) conform IEC 60884-1.
-