








## Afdekraam Gira E2 kleur aluminium



| Specificatie  | Art. nr. | VE     | EUR/stuk excl. BTW | PS | EAN           |
|---|----------|--------|--------------------|----|---------------|
|  1-voudig                     | 0211 25  | 10/100 | 14,69              | 11 | 4010337211259 |
|  1,5-voudig                  | 1001 25  | 10     | 22,00              | 11 | 4010337881346 |
|  2-voudig                    | 0212 25  | 10     | 22,54              | 11 | 4010337212256 |
|  2-voudig zonder middenstijl | 1002 25  | 10     | 22,54              | 11 | 4010337002253 |
|  3-voudig                    | 0213 25  | 1/5    | 36,68              | 11 | 4010337213253 |
|  4-voudig                    | 0214 25  | 1/5    | 59,58              | 11 | 4010337214250 |
|  5-voudig                    | 0215 25  | 1/5    | 90,59              | 11 | 4010337215257 |

### Aanwijzingen

- Ook geschikt voor wandgootinstallatie.
- Afdekraam (1- tot 5-voudig) in combinatie met afdichtset ook geschikt voor installatie spatwaterdicht inbouw IP44.