







Wipschakelaar 10 AX 250 V~ met wip 2-voudig voor weergave hotelkamerstatus



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	1104 01	1	48,41	01	4010337104018
 zuiver wit glanzend	1104 03	1	48,41	01	4010337104032
 zuiver wit mat	1104 27	1	48,41	01	4010337104278
 antraciet	1104 28	1	49,18	11	4010337104285
 kleur aluminium	1104 26	1	53,12	11	4010337104261
 zwart mat	1104 005	1	53,12	11	4010337038535

Kenmerken

- Schakelaar voor weergave hotelkamerstatus "Do not disturb" en "Make up room".
- Met vergrendeling tegen dubbelzijdig inschakelen.
- Elektrisch en mechanisch vergrendeld.

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm ²

Nominaal vermogen

- LEDi/ CFLi:

100 W

Aanwijzingen

- Volgens beschikbaarheid.
