









Wippenet 2-voudig (1+1) beschrijfbaar



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|--|----------|----|--------------------|----|---------------|
|  crème wit glanzend (gelakt) | 2202 01 | 1 | 33,27 | 07 | 4010337012399 |
|  zuiver wit glanzend (gelakt) | 2202 03 | 1 | 33,27 | 07 | 4010337012405 |
|  zuiver wit mat (gelakt) | 2202 27 | 1 | 33,27 | 07 | 4010337013440 |
|  antraciet (gelakt) | 2202 28 | 1 | 36,58 | 07 | 4010337012412 |
|  kleur aluminium (gelakt) | 2202 26 | 1 | 40,34 | 07 | 4010337012429 |
|  zwart mat (gelakt) | 2202 005 | 1 | 40,34 | 07 | 4010337038337 |
|  grijs mat (gelakt) | 2202 015 | 1 | 40,34 | 07 | 4010337083863 |
|  edelstaal | 2132 602 | 1 | 32,09 | 07 | 4010337020103 |

Aanwijzingen

- Dit product kan uitsluitend via de Gira labelservice worden besteld.
- Professionele tekstlabels via de Gira labelservice

www.marking.gira.com.
