









## Wippenet 2-voudig Plus



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend (gelakt)	2192 01	1	30,99	06	4010337012269
 zuiver wit glanzend (gelakt)	2192 03	1	30,99	06	4010337012276
 zuiver wit mat (gelakt)	2192 27	1	30,99	06	4010337013419
 antraciet (gelakt)	2192 28	1	35,15	06	4010337012283
 kleur aluminium (gelakt)	2192 26	1	38,26	06	4010337012290
 zwart mat (gelakt)	2192 005	1	38,26	06	4010337038351
 grijs mat (gelakt)	2192 015	1	38,26	06	4010337083832
 edelstaal	2142 601	1	25,71	06	4010337020141

### Aanwijzingen

- Beschrijfbare wippenets en wippenets zonder tekstkader zijn van metaal, dit kan bij draadloze toepassingen het bereik beperken.