









Luidspreker inbouwradio



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2282 01	1	26,73	03	4010337076230
 zuiver wit glanzend	2282 03	1	26,73	03	4010337076247
 zuiver wit mat	2282 27	1	26,73	03	4010337076254
 antraciet	2282 28	1	28,78	03	4010337076261
 kleur aluminium	2282 26	1	31,35	03	4010337076162
 zwart mat	2282 005	1	31,35	03	4010337037286
 grijs mat	2282 015	1	31,35	03	4010337083931
 edelstaal	2282 600	1	35,98	03	4010337032861

Kenmerken

- Luidspreker voor aansluiting op de Gira inbouwradio.

Technische gegevens

Inbouwdiepte:	32 mm
Aansluitingdoorsnede - Luidspreker-/AUX-aansluiting:	1.5mm ²
Impedantie:	8 Ω
Omgevingstemperatuur:	-5 °C tot +50 °C
