










## Luidspreker inbouwradio RDS



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2282 01 4290409	1	31,35	03	4010337076230
 zuiver wit glanzend	2282 03 4290417	1	31,35	03	4010337076247
 zuiver wit mat	2282 27 4290425	1	31,35	03	4010337076254
 antraciet	2282 28 4290433	1	33,11	03	4010337076261
 kleur aluminium	2282 26 4290391	1	35,77	03	4010337076162
 Zwartglaslook	2282 05 4679833	1	40,75	03	4010337889182
 zwart mat	2282 005 6913664	1	37,38	11	4010337037286
 grijs mat	2282 015	1		11	4010337083931
 edelstaal	2282 600 1146763	1	40,75	03	4010337032861

## Kenmerken

- Luidspreker voor aansluiting op de Gira inbouwradio RDS.

---

## Technische gegevens

Inbouwdiepte:	32 mm
Aansluitingdoorsnede - Luidspreker-/AUX-aansluiting:	1,5 mm <sup>2</sup>
Omgevingstemperatuur:	-5 °C tot +50°C

---