







## Aardlekschakelaar 30 mA



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2664 01 9670504	1	141,67	03	4010337011897
 zuiver wit glanzend	2664 03 9670511	1	141,67	03	4010337011903
 zuiver wit mat	2664 27 9670525	1	141,67	03	4010337011910
 antraciet	2664 28 9670532	1	142,24	03	4010337011927
 kleur aluminium	2664 26 9670518	1	143,68	03	4010337011934
 zwart mat	2664 005 6914371	1	143,68	03	4010337037064

### Kenmerken

- De aardlekschakelaar is een vaste beveiligingsinrichting met spanningsonafhankelijke lekstroomactivering conform VDE 0664.
- Werkingsprincipe komt overeen met dat van een aardlekschakelaar.

### Technische gegevens

Nominale spanning:	AC 230 V, 50/60 Hz
Nominale stroom:	16 A
Nominale lekstroom:	30 mA

Inbouwdiepte: 33 mm  
Omgevingstemperatuur: -25 °C tot +40°C

---

## Aanwijzingen

- Toepassingsgebieden: wandgoten, voor wandcontactdozen zonder aardcontact of in Gira energiezuilen.
  - Montage in een diepe apparaatdoos.
-