

Dubbele wandcontactdoos met randaarde 16 A 250 V~ met verhoogde aanraakbeveiliging (Safety Plus) voor inbouwapparaatdoos 1-voudig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2731 01	1	26,31	01	4010337881100
 zuiver wit glanzend	2731 03	1	26,31	01	4010337881117
 zuiver wit mat	2731 27	10	26,31	01	4010337881124
 antraciet	2731 28	1	29,49	11	4010337000778
 kleur aluminium	2731 26	10	34,41	11	4010337000761
 zwart mat	2731 005	10	34,41	11	4010337037538
 grijs mat	2731 015	1	34,41	11	4010337085256

Technische gegevens

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders van:	1,5 mm ² tot 2,5 mm ²
Omgevingstemperatuur - verhoogde aanraakbeveiliging:	0 °C tot +45 °C

Opbouwhoogte: 17,5 mm

Aanwijzingen

- Passend in alle gangbare apparaatdozen.
 - Verhoogde aanraakbeveiliging (Safety Plus) conform IEC 60884-1.
-