









Wandcontactdoos British Standard (BS 1363) 13 A 250 V~ geschaltet, met sluiters



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|----|--------------------|----|---------------|
|  crème wit glanzend | 2778 01 | 10 | 20,85 | 29 | 4010337079477 |
|  zuiver wit glanzend | 2778 03 | 10 | 20,85 | 29 | 4010337079484 |
|  antraciet | 2778 28 | 10 | 23,46 | 29 | 4010337079507 |
|  kleur aluminium | 2778 26 | 10 | 27,49 | 29 | 4010337079491 |
|  zwart mat | 2778 005 | 10 | 27,49 | 29 | 4010337037750 |
|  grijs mat | 2778 015 | 10 | 27,49 | 29 | 4010337086390 |
|  edelstaal (gelakt) | 2778 600 | 10 | 31,23 | 29 | 4010337022091 |

Kenmerken

- Met schroefklemmen.

Technische gegevens

Inbouwdiepte: 20 mm

Aanwijzingen

- Uitsluitend voor schroefbevestiging.
 - Meer functies en varianten ook voor de 80 mm BS-doos op aanvraag verkrijgbaar.
-