








Wipschakelaar British Standard (BS EN 60669-1) 3-voudig met wippen Uitschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2830 01 4489910	10	19,85	29	4010337830016
 zuiver wit glanzend	2830 03 4489902	10	19,85	29	4010337830030
 antraciet	2830 28 4489878	10	21,85	29	4010337830283
 kleur aluminium	2830 26 4489886	10	24,86	29	4010337830269
 zwart mat	2830 005 6914378	10	24,86	29	4010337038580
 grijs mat	2830 015	10	24,86	29	4010337087113
 edelstaal (gelakt)	2830 600 3626968	10	27,65	29	4010337022022

Technische gegevens

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm ²
Nominaal vermogen:	100 W ledbelasting (IEC 60669)