








Wipschakelaar British Standard (BS EN 60669-1) 3-voudig met wippen Schakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2830 01	10	24,06	29	4010337830016
 zuiver wit glanzend	2830 03	10	24,06	29	4010337830030
 antraciet	2830 28	10	26,49	29	4010337830283
 kleur aluminium	2830 26	10	30,13	29	4010337830269
 zwart mat	2830 005	10	30,13	29	4010337038580
 grijs mat	2830 015	10	30,13	29	4010337087113
 edelstaal (gelakt)	2830 600	10	33,51	29	4010337022022

Technische gegevens

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm ²
Nominaal vermogen:	100 W ledbelasting (IEC 60669)