








Wipschakelaar British Standard (BS EN 60669-1) 3-voudig met wippen Universele uit-wisselschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2832 01	10	35,18	29	4010337832010
 zuiver wit glanzend	2832 03	10	35,18	29	4010337832034
 antraciet	2832 28	10	37,81	29	4010337832287
 kleur aluminium	2832 26	10	41,83	29	4010337832263
 zwart mat	2832 005	10	51,99	11	4010337038528
 grijs mat	2832 015	10	51,99	11	4010337087120
 edelstaal (gelakt)	2832 600	10	45,56	29	4010337022053

Kenmerken

- Met schroefklemmen.

Technische gegevens

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm ²

Aanwijzingen

- Uitsluitend voor schroefbevestiging.
-