








**Wipschakelaar British Standard (BS EN 60669-1) 3-voudig met wippen
Universele uit-wisselschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2832 01	10	34,09	29	4010337832010
 zuiver wit glanzend	2832 03	10	34,09	29	4010337832034
 antraciet	2832 28	10	36,64	29	4010337832287
 kleur aluminium	2832 26	10	40,53	29	4010337832263
 zwart mat	2832 005	10	50,62	11	4010337038528
 grijs mat	2832 015	10	50,62	11	4010337087120
 edelstaal (gelakt)	2832 600	10	44,15	29	4010337022053

Kenmerken

- Met schroefklemmen.

Technische gegevens

Inbouwdiepte: 25 mm

Aansluitingdoorsnede
- voor geleiders tot: 2.5mm²

Aanwijzingen

- Uitsluitend voor schroefbevestiging.
