








**Wipschakelaar British Standard (BS EN 60669-1) 20 AX 250 V~ met wip
Schakelaar 2-polig**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2836 01	10	36,40	29	4010337078944
 zuiver wit glanzend	2836 03	10	36,40	29	4010337078951
 antraciet	2836 28	10	37,07	29	4010337078975
 kleur aluminium	2836 26	1	40,02	29	4010337078968
 zwart mat	2836 005	10	40,02	29	4010337038566
 grijs mat	2836 015	10	40,02	29	4010337087144
 edelstaal	2836 600	10	46,50	29	4010337021933

Kenmerken

- Met schroefklemmen.

Technische gegevens

Inbouwdiepte:	24 mm
Aansluitingdoorsnede - voor geleiders tot:	2 x 4 mm ² of 1 x 6 mm ²

Aanwijzingen

- Uitsluitend voor schroefbevestiging.
 - BS EN 60669-1.
-