








**Wipdrukcontact 3-voudig 10 A 250 V~met wippen  
Maakcontact 1-polig**

| Specificatie  | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|---|----------|----|--------------------|----|---------------|
|  crème wit glanzend   | 2844 01  | 10 | 35,86              | 29 | 4010337082033 |
|  zuiver wit glanzend | 2844 03  | 10 | 35,86              | 29 | 4010337082040 |
|  antraciet           | 2844 28  | 10 | 38,46              | 29 | 4010337082064 |
|  kleur aluminium     | 2844 26  | 10 | 42,29              | 29 | 4010337082057 |
|  zwart mat           | 2844 005 | 10 | 42,29              | 29 | 4010337037903 |
|  grijs mat           | 2844 015 | 10 | 42,29              | 29 | 4010337087182 |
|  edelstaal (gelakt)  | 2844 600 | 10 | 45,92              | 29 | 4010337021957 |

**Kenmerken**

- Met schroefklemmen.

## Technische gegevens

Inbouwdiepte: 25 mm

Aansluitingdoorsnede  
- voor geleiders tot: 2.5mm<sup>2</sup>

---

## Aanwijzingen

- Uitsluitend voor schroefbevestiging.

---